



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Thread	² h ₁	b	d ₂	d ₃	d ₄ Thread	h ₂	h ₃	h ₄	k
M 16	55 2.17	50 1.97	42 1.65	60 2.36	M 5	20 .79	33 1.30	61 2.40	40 1.57
M 16	90 3.54	50 1.97	42 1.65	60 2.36	M 5	20 .79	33 1.30	93 3.66	40 1.57
M 20	69 2.72	50 1.97	50 1.97	70 2.76	M 6	25 .98	41 1.61	77 3.03	50 1.97
M 20	109 4.29	50 1.97	50 1.97	70 2.76	M 6	25 .98	41 1.61	116 4.57	50 1.97

Specification

- Compression plate
Steel, hardened and zinc plated
Property strength class 8.8
- Support screw and fastening hardware
Steel, hardened and blackened finish
Property strength class 8.8
- *Strength Values of Screws* → page QVX
- RoHS compliant

Information

No. 6312 S support extensions are screwed into the adjustable holder of the crocodile clamp to increase the clamping height.

see also...

- *Crocodile Clamps NO. 6312 V* → page QVX
- *Crocodile Clamps NO. 6312 VS (with Clamping Stud)* → page QVX
- *Crocodile Clamps NO. 6312 VT (with Clamping Bolt)* → page QVX

How to order

¹ ²
NO.6312S-M16-55

- 1 Thread d₁
- 2 Height h₁

