



**3 Type**  
**A** Without dipstick  
**B** With dipstick

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Pipe thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
41 1.61	G 1/2	5 0.20	12 0.47	20 0.79	180 7.09
41 1.61	G 3/4	5 0.20	12 0.47	20 0.79	180 7.09
51 2.01	G 1	5 0.20	13 0.51	24 0.94	180 7.09
61 2.40	G 1 1/4	5 0.20	14 0.55	28 1.10	180 7.09
71 2.80	G 1 1/2	5 0.20	15 0.59	32 1.26	180 7.09

**Specification**

- Body  
Nylon plastic  
- Screw-fit  
- Black  
- Temperature resistant up to 158 °F (70 °C)
- Seal  
Synthetic rubber, fluid resistant
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**Information**

TA3-7 breather valve caps are provided with a fluid symbol and no dipstick markings.  
 Complete with unmounted seal.

see also...

- *Breather Valve Caps TA1-2 (with Fine Thread)* → [www.jwwinco.com](http://www.jwwinco.com)

How to order

**1** **2** **3**  
**TA3-7-41-G1/2-A**

<b>1</b>	Diameter d <sub>1</sub>
<b>2</b>	Pipe thread d <sub>2</sub>
<b>3</b>	Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

