



3 Type

- J Without symbol (for TAO)
- K With fluid symbol (for TCA)

4 Identification no.

- 1 Without vent hole

Metric table

Dimensions in: millimeters - inches

1 s	2 d ₁ Pipe thread	d ₂	l ₁	l ₂	l ₃
17 0.67	G 1/4	5 0.20	10 0.39	16 0.63	190 7.48
22 0.87	G 1/4	5 0.20	10 0.39	17 0.67	190 7.48
22 0.87	G 3/8	5 0.20	11 0.43	18 0.71	191 7.52
26 1.02	G 1/2	5 0.20	12 0.47	19 0.75	192 7.56
32 1.26	G 3/4	5 0.20	12 0.47	20 0.79	192 7.56
38 1.50	G 1	5 0.20	13 0.51	22 0.87	193 7.60

Specification

- Body
Nylon plastic
- Black finish
- Temperature resistant up to 158 °F (70 °C)
- Dipstick
Steel, zinc plated
- Plastic Characteristics → page QVX
- RoHS compliant

Information

TAO fluid plugs are provided without a symbol, TCA fluid plugs are provided with a fluid symbol. Both have no dipstick markings.

see also...

- Fluid Fill / Drain Plugs TO (without Dipstick) → page QVX

How to order (Without symbol)	1 Width s
1 2 3 4 TAO-22-G3/8-J-1	2 Pipe thread d ₁
	3 Type
	4 Identification no.

How to order (With fluid symbol)	1 Width s
1 2 3 4 TCA-38-G1-K-1	2 Pipe thread d ₁
	3 Type
	4 Identification no.