



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂		³ Length l	d ₃	h	t
1.13 28.7	1/4 x 20	-	0.56 14.2	0.50 12.7	0.75 19.1	0.38 9.7
1.50 38.1	5/16 x 18	-	0.75 19.1	0.63 16.0	0.88 22.4	0.50 12.7
2.00 50.8	5/16 x 18	3/8 x 16	0.75 19.1	0.75 19.1	1.00 25.4	0.50 12.7

Specification

- Three-lobed knob
Phenolic plastic
 - Temperature resistant up to 300 °F (150 °C)
 - Black, shiny finish
- Tapped insert
Brass
- Threaded stud
Steel
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

TPK and TPKS three-lobed knobs are an economical choice for a variety of light duty applications.

How to order (Brass tapped insert) ¹ ² TPK-2.00-3/8X16	1	Handle diameter d ₁
	2	Thread d ₂
How to order (Steel threaded stud) ¹ ² ³ TPKS-1.50-5/16X18-0.75	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l

1.1 1.2 1.3 1.4 2.1 2.2 2.3 2.4

