



Metric table

Dimensions in: millimeters - inches

1	2	3					d ₃	h ₁	h ₂
d ₁	d ₂	Length l							
45 1.77	M 6	15 0.59	20 0.79	25 0.98	30 1.18	40 1.57	18 0.71	27 1.06	16 0.63
45 1.77	M 8	15 0.59	20 0.79	30 1.18	40 1.57	-	18 0.71	27 1.06	16 0.63
45 1.77	M 10	20 0.79	30 1.18	-	-	-	18 0.71	27 1.06	16 0.63
55 2.17	M 6	20 0.79	25 0.98	40 1.57	-	-	20 0.79	33 1.30	19 0.75
55 2.17	M 8	20 0.79	30 1.18	40 1.57	-	-	20 0.79	33 1.30	19 0.75
55 2.17	M 10	15 0.59	20 0.79	30 1.18	-	-	20 0.79	33 1.30	19 0.75

Specification

- Three-lobed knob
Nylon plastic
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Threaded stud
Steel, zinc plated
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Stainless steel insert

Information

V3-B-P three-lobed knobs have an aesthetically pleasing shape, provide a comfortable grip and expand the range of clamping options.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Three-Lobed Knobs V3-B (with Brass Blind Tapped Insert) → page 654
- Three-Lobed Knobs V3-B-FP (with Brass Through Tapped Insert) → page 654

How to order	1	Handle diameter d ₁
V3-B-P-45-M10-30	2	Thread d ₂
	3	Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4