



3 Type
D With revolving handle

Universal table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Pilot hole	b	d ₃	d ₄	d ₅ Thread	d ₆	l ₁	l ₂	l ₃	l ₄	l ₅	r	s
150 5.91	P 6	18 0.71	32 1.26	26 1.02	M 10	28 1.10	37 1.46	13 0.51	48 1.89	80 3.15	128 5.04	65 2.56	20 0.79

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 300 °F (150 °C)
- Black
- Hub bushing
Stainless steel AISI 303
- Revolving handle
Plastic
Duroplast (Phenolic PF)
- Black, shiny finish
- Threaded spindle
Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

VPRA-MS disk handwheels with revolving handle are distinguished by modern design. An excellent choice for light-medium duty applications.

see also...

- Countersunk Washers GN 184 (for Axial Fixing) → page 1150

How to order

VPRA-MS-150-P6-D

- 1** Handwheel diameter d₁
- 2** Pilot hole d₂
- 3** Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

