



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	³ Length l				d ₃	h ₁	h ₂
22 0.87	M 5	10 0.39	15 0.59	25 0.98	-	15 0.59	13 0.51	4 0.16
22 0.87	M 6	10 0.39	15 0.59	20 0.79	30 1.18	15 0.59	13 0.51	4 0.16
26 1.02	M 5	10 0.39	-	-	-	20 0.79	16 0.63	6 0.24
26 1.02	M 6	15 0.59	25 0.98	-	-	20 0.79	16 0.63	6 0.24
26 1.02	M 8	25 0.98	-	-	-	20 0.79	16 0.63	6 0.24

Specification

- Body
Phenolic plastic
- Temperature resistant up to 302 °F (150 °C)
- Black, shiny finish
- Threaded stud
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- RoHS compliant

Information

For slip-free fastening and clamping, these VPZ knurled screws are an excellent economical choice.

see also...

- *Knurled Nuts VBZ (with Brass Tapped Insert)* → page 689

How to order

¹ ² ³
VPZ-22-M6-20

¹	Handle diameter d ₁
²	Thread d ₂
³	Length l