



Universal table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Pilot hole	d ₃	d ₄	b	l ₁	l ₂	l ₃	l ₄
60 2.36	P 4	20 0.79	30 1.18	16 0.63	32 1.26	16 0.63	10 0.39	15 0.59
75 2.95	P 4	24 0.94	34 1.34	20 0.79	39 1.54	19 0.75	11 0.43	22 0.87
90 3.54	P 6	32 1.26	44 1.73	20 0.79	42 1.65	22 0.87	12 0.47	25 0.98

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 266 °F (130 °C)
- Black, shiny finish
- Hub bushing
Steel, zinc plated
- Keyways WN / DIN 6885 → page XYZ / XYZ
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Other modifications such as inch and metric blind bores, threads, etc.

Information

VU five-lobed control knobs are ideally suited for light-medium duty adjusting or clamping applications.

see also...

- Five-Lobed Control Knobs VUA → page 278
- Five-Lobed Control Knobs VUM → page 279

How to order ¹ ² VU-60-P4	1 Knob diameter d ₁
	2 Pilot hole d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

