



### Inch table



Dimensions in: inches - millimeters

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h	k	Length l	Load bearing capacity
3/8 x 16	0.88 22.4	2.00 50.8	1.25 31.8	2.50 63.5	0.38 9.7	0.63 16.0	2700 lbf 12010 N
1/2 x 13	0.88 22.4	2.00 50.8	1.25 31.8	2.50 63.5	0.38 9.7	0.63 16.0	2700 lbf 12010 N
5/8 x 11	1.38 35.1	2.50 63.5	1.50 38.1	3.00 76.2	0.50 12.7	0.75 19.1	5000 lbf 22241 N
3/4 x 10	1.38 35.1	2.50 63.5	1.50 38.1	3.00 76.2	0.50 12.7	0.75 19.1	5000 lbf 22241 N

### Specification

- Carbon steel 1030
- Forged
- Zinc plated



### Information

**ST**

WN 583 eye nuts offer a high load bearing capacity and are tested to meet high safety standards.

see also...

- *Lifting Eye Bolts WN 580 (Inch Size)* → page 1582
- *Lifting Eye Nuts DIN 582 (Metric Size)* → page 1584
- *Safety Swivel Lifting Eye Nuts GN 583 (Metric Size)* → [www.jwwinco.com](http://www.jwwinco.com)

How to order

**WN 583-3/8X16-ST**

1 Thread d<sub>1</sub>

2 Material

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

