



Inch table

Dimensions in: inches - *millimeters*

T-slot width	d Thread	Length l - Thread length b						a	e	k
		l - b	l - b	l - b	l - b	l - b	l - b			
1 25.4	1 x 8	4 - 2.56 101.6 - 65.0	4.5 - 2.76 114.3 - 70.1	6 - 4.33 152.4 - 110.0	8 - 4.92 203.2 - 125.0	10 - 5.91 254.0 - 150.1	12 - 7.48 304.8 - 190.0	0.92 23.4	1.65 41.9	0.63 16.0

Specification

- Heat-treatable steel
 - Property class 10.9
 - Forged
 - Milled T-slot guide face
- *Strength Values of Screws* → page 2127
- RoHS compliant

Information

- see also...
- *T-Slot Bolts DIN 787 (Metric Size)* → page 1229

How to order	1 T-slot width
WN 787 - 1 - 1X8 - 6	2 Thread d
	3 Length l