



Inch table

d ₁ ∅	d ₂	l ₁ ≈	l ₂
D 1/2	0.484 12.3	0.424 10.8	0.150 3.8
D 5/8	0.578 14.7	0.433 11.0	0.150 3.8
D 3/4	0.698 17.7	0.443 11.3	0.140 3.6
D 1.00	0.940 23.9	0.433 11.0	0.150 3.8
D 1 1/4	1.190 30.2	0.512 13.0	0.220 5.6
D 1 1/2	1.443 36.7	0.512 13.0	0.220 5.6
D 2 1/2	2.415 61.3	0.680 17.3	0.220 5.6

Dimensions in: inches - millimeters

s ₁ □	s ₂	l ₁ ≈	l ₂
V 1/2	0.458 11.6	0.470 11.9	0.150 3.8
V 5/8	0.574 14.6	0.470 11.9	0.150 3.8
V 3/4	0.693 17.6	0.445 11.3	0.155 3.9
V 1.00	0.950 24.1	0.444 11.3	0.160 4.1
V 1 1/4	1.193 30.3	0.445 11.3	0.165 4.2
V 1 1/2	1.440 36.6	0.577 14.7	0.175 4.4

Specification

- Plastic
Technopolymer (Polyethylene PE)
Black, matte finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

WN 991 end plugs for standard round and square tubes are designed to fit multiple tube gauges with a secure fit.

They are ideal for office and patio furniture, tubular racks or structures, appliances, exercise equipment, or anywhere a finished look is needed.

The plugs feature multiple horizontal ribs with built-in flexibility for easy installation.

see also...

- *Threaded Tube Ends EN 348 (Plastic, Square Type)* → page 1580
- *Threaded Tube Ends EN 448 (Plastic, Round Type)* → page 1578
- *Threaded Tube Ends EN 448 (Plastic, Square Type)* → page 1576
- *Threaded Tube Ends GN 992 (Aluminum)* → page 1581
- *Threaded Tube Ends GN 992.5 (Stainless Steel)* → page 1581

How to order (For round tubes)	1	Diameter d ₁
WN991-D1/2		
How to order (For square tubes)	1	Square s ₁
WN991-V3/4		

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10