



Metric table

Dimensions in: millimeters - inches

d₁	d₂ Thread				d₃ Bore	d₄	d₅ Thread	h₁	h₂	t₁	t₂
22 0.87	M 4	M 5	M 6	M 8	B 6	15 0.59	M 4	14 0.55	6 0.24	8 0.31	9 0.35
24 0.94	M 4	M 5	M 6	M 8	B 6	15 0.59	M 4	14 0.55	6 0.24	8 0.31	9 0.35
26 1.02	M 4	M 5	M 6	M 8	B 6	16 0.63	M 4	15 0.59	6 0.24	8 0.31	8 0.31

Specification

- Body
Nylon plastic
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

More shock proof than their phenolic counterpart, these ZB knurled nuts provide excellent slip-free clamping and fastening.

see also...

- *Knurled Nuts ZB-FP (with Brass Tapped Through Insert)* → www.jwwinco.com

How to order

ZB-22-B6

- 1 Handle diameter **d₁**
- 2 Bore **d₃** (Thread **d₂**)