



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>				d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t
22 0.87	M 4	M 5	M 6	M 8	15 0.59	9 0.35	14 0.55	6 0.24	11 0.43
24 0.94	M 4	M 5	M 6	M 8	15 0.59	9 0.35	14 0.55	6 0.24	11 0.43
26 1.02	M 4	M 5	M 6	M 8	16 0.63	9 0.35	15 0.59	6 0.24	11 0.43

**Specification**

- Nylon plastic
  - Temperature resistant up to 230 °F (110 °C)
  - Black, matte finish
- Tapped insert  
Brass, molded-in
- *Plastic Characteristics* → page QVX
- RoHS compliant

**Information**

More shock proof than their phenolic counterpart, these ZB-FP knurled nuts provide excellent slip-free clamping and fastening.

see also...

- *Knurled Nuts ZB (with Brass Tapped or Plain Blind Bore Insert)* → page QVX

How to order <sup>1</sup> <sup>2</sup> <b>ZB-FP-24-M5</b>	1 Handle diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>