



- Metric**
- 1 Type**
- SG** With star knob
  - SK** With wing knob
  - ST** With T-handle
  - RG** With hollow knurled knob GN 7336
  - KG** With wing knob
  - HG** With lever
  - LG** With lever (only with housing collar in SW)

**Metric table**

**2** Dimensions in: millimeters - inches

Latch arm distance <b>A</b>											<b>d</b>	<b>h</b>		
4	8	13	16	20	24	28	32	36	40	45	Type SG, RG, KG, HG	Type SK, ST, LG	Type SG, RG, KG, HG	Type SK, ST, LG
0.16	0.31	0.51	0.63	0.79	0.94	1.10	1.26	1.42	1.57	1.77	28	32	4	6
0.24	0.39	0.55	0.71	0.87	1.02	1.18	1.34	1.50	1.65	1.97	28	32	4	6

**Specification**

- Cam latch housing  
Zinc die-cast  
Housing collar  
- Chrome plated finish  
- Powder coated  
Black, RAL 9005, textured finish **● SW**
- Latch arm / assembly hardware  
Steel, zinc plated, blue passivated finish
- Operating elements  
- Type SG, SK, ST, RG, KG, HG  
Plastic  
Technopolymer (Polyamide PA)  
Black, matte finish  
- Type LG  
Zinc die-cast, powder coated  
Black, RAL 9005, textured finish
- Cover cap (Type RG, KG, HG, LG)  
Plastic  
Technopolymer (Polyamide PA)  
Light gray
- Protection class IP65
- IP Protection Classes → page XYZ
- RoHS compliant

**Information**

GN 115 cam latches lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm.

Products comes supplied with a loosely enclosed latch arm.

see also...

- List of Cam Latch / Cam Lock Types → page 1256
- Cam Latches GN 115 (Operation with Socket Key) → page 1263
- Cam Locks GN 115 → page 1263
- Cam Latches GN 115 (Stainless Steel) → page 1267
- Protective guide plates GN 120.2 → www.jwwinco.com

How to order (Chrome plated housing collar)	<b>1</b> Type
<b>GN 115-SG-20</b>	<b>2</b> Latch arm distance A

How to order (Powder coated housing collar)	<b>1</b> Type
<b>GN 115-HG-32-SW</b>	<b>2</b> Latch arm distance A
	<b>3</b> Finish (Housing collar)