



Metric



3 Type

F With fixed handle

Metric table

1

2

Dimensions in: millimeters / inches

No.	d ₁ H7 Bore	d ₂	d ₃	d ₄	d ₅	h ₁	h ₂ ≈	Length l
100	B 7	13 0.51	16 0.63	18 0.71	10 0.39	13 0.51	31 1.22	25 0.98
101	B 8	15 0.59	19 0.75	20 0.79	13 0.51	17 0.67	40 1.57	28 1.10
102	B 8	16 0.63	20 0.79	22 0.87	14 0.55	17 0.67	45 1.77	34 1.34
103	B 10	18 0.71	23 0.91	25 0.98	16 0.63	19.5 0.77	50 1.97	41 1.61
104	B 12	20 0.79	26 1.02	28 1.10	18 0.71	21.5 0.85	56 2.20	50 1.97

Specification

Body

- Steel
- Fine turned
- Zinc plated, blue passivated finish

Fixed Handle DIN 39

- Steel
- Zinc plated, blue passivated finish

RoHS

On request

- Other modifications such as inch and special metric bores, blind bores, keyways, set screw holes, etc.

Tri-ball handles GN 10 allow fine adjustment.

Alternatives with modern design are control crank handles EN 510 and control handles GN 112.1.

see also...

	Page
EN 510 Control Crank Handles (Plastic)	QVX
GN 112.1 Control Crank Handles (Zinc Die-Cast)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
----------------------------	-----

How to order

GN 10-100-B7-F

1 No.	
2 Bore d ₁	
3 Type	