



Specification



- Lever body
Zinc die-cast
- Powder coated
Black, RAL 9005, textured finish **SW**
Orange, RAL 2004, textured finish **OS**
- Threaded stud / retaining screw
Steel
- Blackened finish
- Property class 5.8
- Strength Values of Screws → page 2127
- [RoHS compliant](#)

On request

- Special colors, stud lengths, and threads

Information

GN 101 adjustable levers have proven to be ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- [Adjustable Levers GN 101.1 \(Stainless Steel Threaded Stud\) → page 484](#)
- [Adjustable Levers GN 300 \(Blackened Steel Threaded Stud\) → page 408](#)
- [Straight Adjustable Levers GN 302 \(Blackened Steel Threaded Stud\) → page 454](#)
- [Adjustable Levers GN 300.2 \(Zinc Plated Steel Threaded Stud\) → page 410](#)
- [Adjustable Levers EN 602.1 \(Stainless Steel Threaded Stud\) → page 490](#)
- [Adjustable Levers EN 503 \(Plastic Lever Body\) → page 514](#)

How to order (Inch)	1 Diameter d ₁
GN 101-14-10X32-10-SW	2 Thread d ₂
	3 Thread length l ₁
	4 Color
How to order (Metric)	1 Diameter d ₁
GN 101-22-M10-40-OS	2 Thread d ₂
	3 Thread length l ₁
	4 Color

Inch table

Dimensions in: inches - *millimeters*

d ₁	d ₂	l ₁									d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂
		0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-						
0.55 14	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45
0.55 14	10 x 24	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45
0.55 14	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45
0.71 18	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	-	-	-	-	-	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62
0.71 18	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62
0.71 18	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62
0.87 22	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	1.42 36	0.31 8	2.05 52	0.16 4	2.91 74
0.87 22	1/2 x 13	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	-	-	0.63 16	1.42 36	0.31 8	2.05 52	0.16 4	2.91 74
0.98 25	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.75 19	1.69 43	0.43 11	2.48 63	0.16 4	3.50 89
0.98 25	1/2 x 13	0.63 16	0.79 20	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	0.75 19	1.69 43	0.43 11	2.48 63	0.16 4	3.50 89
1.18 30	1/2 x 13	0.98 25	1.26 32	1.57 40	1.97 50	2.17 55	2.48 63	-	-	-	0.91 23	1.99 50.5	0.47 12	2.99 76	0.20 5	4.25 108
1.18 30	5/8 x 11	1.26 32	1.57 40	1.97 50	2.17 55	2.48 63	-	-	-	-	0.91 23	1.99 50.5	0.47 12	2.99 76	0.20 5	4.25 108

Metric table

Dimensions in: millimeters - *inches*

d ₁	d ₂	l ₁									d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂
		12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15						
14 0.55	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	25 0.98	4.5 0.18	35 1.38	3.5 0.14	45 1.77	
18 0.71	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	31 1.22	6.5 0.26	45 1.77	4 0.16	62 2.44	
22 0.87	M 10	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	36 1.42	8 0.31	52 2.05	4 0.16	74 2.91	
25 0.98	M 12	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	19 0.75	43 1.69	11 0.43	63 2.48	4 0.16	89 3.50	
30 1.18	M 16	-	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	23 0.91	50.5 1.99	12 0.47	76 2.99	5 0.20	108 4.25	

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

