


Application examples



Cam door latches GN 119

Cam latches GN 115

Metric table

Dimensions in: millimeters - inches

d ₁	b	h ₁	h ₂	Length l	s	Usable for * d ₂	GN 115	GN 115.8	GN 115.9	GN 119 SST	GN 119 ST	GN 315.1	GN 515	GN 516	GN 516.1	GN 516.5	
31 1.22	2 0.08	6 0.24	18 0.71	35 1.38	20.5 0.81	28 1.10	x	x	x	x	-	-	-	-	-	-	-
35 1.38	2 0.08	8 0.31	18 0.71	36 1.42	20.5 0.81	30 / 32 1.18 / 1.26	-	-	-	-	x	x	x	x	x	x	x

* Used for latches actuated by key / socket key

Specification

- Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Plastic Characteristics → page QVX
- RoHS compliant



Information

GN 120.1 finger grip opening handles are simple operating elements that are used in combination with cam locks or cam latches. They have a low installation height and can be mounted as required in a 90° grid pattern together with the latch housing.

Please note: The clamping range A1 ... A9 and / or the latch distance A is reduced by the dimension b.

see also...

- List of Cam Latch / Cam Lock Types → page XYZ
- Protective Guide Plates GN 120.2 → page XYZ
- Internal Cabinet Handles GN 120.3 → page XYZ

How to order

GN 120.1-31-SW

1 Outside diameter d

2 Color

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

