



- 1 Type**
- DK** With triangular spindle
 - VK7** With square spindle
 - VK8** With square spindle
 - SCH** With slot
 - VDE** With double bit
- 3 Identification no.**
- 1** Operation in the illustrated position top left
 - 2** Operation in the illustrated position top right

Metric table

Dimensions in: millimeters - inches

Latch arm distance A																					
4	6	8	10	13	14	16	18	20	22	24	26	28	30	32	34	36	38	40	42	45	50
0.16	0.24	0.31	0.39	0.51	0.55	0.63	0.71	0.79	0.87	0.94	1.02	1.10	1.18	1.26	1.34	1.42	1.50	1.57	1.65	1.77	1.97

Specification

- Front frame
Zinc die-cast
Powder coated
Black, RAL 9005, textured finish **●SW**
Silver, RAL 9006, textured finish **●SR**
- Tray
Plastic
- Black-gray (for SW)
- Light gray (for SR)
- Cam latch housing
Zinc die-cast
- Black powder coated (for SW)
- Chrome plated finish (for SR)
- Latch arm / assembly hardware
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

GN 115.10 cam latches are used in applications that require a molded recess in addition to the latching mechanism, e.g. if operating elements are not allowed to protrude for reasons of space.

They lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm.

Product comes supplied with a loosely enclosed latch arm.

The socket key latches the latch arm and provides security from accidentally opening but does not lock the arm in place.

A socket key is not included.

see also...

- *List of Cam Latch / Cam Lock Types* → page 1256
- *Cam Latches GN 115.7 (with Cabinet "U" Handle)* → page 1274
- *Cam Locks GN 115.10 (with Gripping Tray)* → page 1278
- *Ledge Handles with Cam Latch / Cam Lock EN 932* → www.jwwinco.com

Accessory

- Socket keys GN 119.2 → page 1310
- Protective guide plates GN 120.2 → page XYZ

How to order

1	Type
2	Latch arm distance A
3	Identification no.
4	Color

GN 115.10-SCH-20-2-SR