



- 3 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

**Metric table**

<b>d<sub>1</sub> - d<sub>2</sub></b>				<b>k</b> Clamping length	<b>d<sub>3</sub></b> Mounting screws on the drive key	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>m</b>	<b>z</b> Screw locations for screw size	<b>Accessory</b> Recommended lever GN 911 for z l <sub>3</sub>	
One-axis system <b>GN 132.1</b>	Two-axis system <b>GN 132.2</b>										
Without sleeve bearing B30 - B30	With sleeve bearing G30 - B30	Without sleeve bearing B30 - B30	With sleeve bearing G30 - G30	40 1.57	M 4	97 3.82	40 1.57	33 1.30	M8-25	63 2.48	78 3.07
B30 - B30	G30 - B30	B30 - B30	G30 - G30	56 2.20	M 4	125 4.92	56 2.20	45 1.77	M10-35	-	-
B40 - B40	G40 - B40	B40 - B40	G40 - G40	56 2.20	M 5	125 4.92	56 2.20	45 1.77	M10-35	78 3.07	92 3.62
B40 - B40	G40 - B40	B40 - B40	G40 - G40	65 2.56	M 5	143 5.63	65 2.56	53 2.09	M10-50	-	-
B50 - B50	G50 - B50	B50 - B50	G50 - G50	65 2.56	M 6	143 5.63	65 2.56	53 2.09	M10-50	78 3.07	92 3.62
B60 - B60	G60 - B60	B60 - B60	G60 - G60	80 3.15	M 8	169 6.65	80 3.15	65 2.56	M10-50	78 3.07	92 3.62

Dimensions in: millimeters - inches

**Specification**

- Body  
Aluminum  
Powder coated  
Black, RAL 9005, textured finish **S**
- Sleeve bearing  
Plastic (PTFE)
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

GN 132.1 and GN 132.2 two-way linear actuator connectors are based on two-way connector clamps. The additionally provided mounting holes are used to connect to the drive key of a linear actuator. Bores with the designation "G" are equipped with sleeve bearings.

With the screw locations **z**, the play of the guide bores **d<sub>1</sub> / d<sub>2</sub>** can be adjusted or the linear actuator connector can be clamped after adjustment.

For quick clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

**see also...**

- *Linear Actuators GN 291* → page 1948
- *Linear Actuators GN 292* → [www.jwwinco.com](http://www.jwwinco.com)
- *Linear Actuators GN 293* → [www.jwwinco.com](http://www.jwwinco.com)

**Accessory**

- Adjustable levers GN 911 → page 1810

**On request**

- Inch size bores

<b>How to order (One-axis system)</b>	<b>1</b> Bore <b>d<sub>1</sub> - d<sub>2</sub></b>
<b>GN 132.1-G40-B40-56-2-S</b>	<b>2</b> Clamping length <b>k</b>
	<b>3</b> Identification no.
	<b>4</b> Finish

  

<b>How to order (Two-axis system)</b>	<b>1</b> Bore <b>d<sub>1</sub> - d<sub>2</sub></b>
<b>GN 132.2-G50-G50-65-2-S</b>	<b>2</b> Clamping length <b>k</b>
	<b>3</b> Identification no.
	<b>4</b> Finish

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10