



1 Type

RG With hollow knurled knob GN 7336

KG With wing knob

HG With lever

Metric table

2

Dimensions in: millimeters - inches

| Latch arm distance A | | | | | | | | | | | | | | |
|----------------------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| 4 | 6 | 8 | 10 | 13 | 14 | 16 | 18 | 20 | 22 | 24 | 26 | 28 | 30 | 32 |
| 0.16 | 0.24 | 0.31 | 0.39 | 0.51 | 0.55 | 0.63 | 0.71 | 0.79 | 0.87 | 0.94 | 1.02 | 1.10 | 1.18 | 1.26 |

Specification

3

- Cam latch housing
Zinc die-cast
Housing collar
Powder coated
Black, RAL 9005, textured finish **● SW**
- Latch arm / assembly hardware
Steel, zinc plated, blue passivated finish
- Operating elements
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- Cover cap
Plastic
Technopolymer (Polyamide PA)
Light gray, matte finish
- Other parts
Steel
Zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

GN 115.9 safety cam latches have a **push-to-turn** safety function. In the two end positions the spindle is locked in place by the cam latch. The latch arm can be turned 90° (a quarter of a turn) only when the hand operating element is pushed in, which releases the safety pin from the locked position. This feature protects the latch arm from moving on its own or as the result of vibrations.

The beveled edges of the latch arm create a smooth latching of the door. The 15 different off-set latch arm options allow the "Latch arm distance A" to be set between 4 mm and 32 mm.

The safety cam latches GN 115.9 comes supplied with a loosely enclosed latch arm.

see also...

- *Construction and Assembly Instructions* → page 1261
- *List of Cam Latch / Cam Lock Types* → page 1256

Accessory

- Protective guide plates GN 120.2
→ www.jwwinco.com

How to order

GN 115.9-HG-32-SW

| | |
|----------|-------------------------|
| 1 | Type |
| 2 | Latch arm distance A |
| 3 | Finish (Housing collar) |