



SS Stainless Steel

3 Type

- A** Without seals
- B** With seals

4 Identification no.

- 4** With 2 stainless steel cap nuts DIN 917

Metric table

1 d_1 Bore	2 d_2 Bore	b	d_3	k Clamping length	l_1	m	z Screw locations for screw size	Accessory Recommended lever GN 911.3 for z l_2	
B 30	B 30	22 0.87	37 1.46	40 1.57	104 4.09	33 1.30	M 8	63 2.48	78 3.07
B 40	B 40	28 1.10	50.3 1.98	56 2.20	133 5.24	45 1.77	M 10	78 3.07	92 3.62
B 50	B 50	30 1.18	60 2.36	65 2.56	150 5.91	53 2.09	M 10	78 3.07	92 3.62

Dimensions in: millimeters - inches

Specification

- Body
Stainless steel AISI CF-8
Matte shot-blasted finish
- Carriage bolts DIN 603
Stainless steel A2
- Cap nuts DIN 917 / washers
Stainless steel A2
- Seals
 - Sealing disks
Plastic (Polyacetal POM)
 - Spacer ring
Silicone, 40 ... 60 shore A
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Adjustable levers GN 911.3 → page QVX

Information

The clamping bores of GN 132.5 two-way connector clamps are mechanically machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw locations z , carriage bolts and cap nuts reduce the bore cross-section for clamping. Type B is equipped with seals at the screw locations.

For clamping without tools, the cap nuts can be replaced by GN 911.3 adjustable levers listed in the table as accessory.

see also...

- *Construction Tubes GN 990* → page QVX

How to order

GN 132.5-B30-B30-A-4

- 1** Bore d_1
- 2** Bore d_2
- 3** Type
- 4** Identification no.

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10