



Inch table

Dimensions in: inches - millimeters

1			2			3											
l_1	d_1		l_2			d_3	d_4	h_1	h_2	h_3	h_4						
											Stroke						
4.72 120	3/8 x 16	1/2 x 13	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.63 16	1.26 32	1.16 29.5	0.08 2	1.63 41.5	0.10 2.5		
5.71 145	5/8 x 11	-	1.26 32	1.57 40	1.97 50	2.48 63	3.15 80	-	-	0.91 23	1.57 40	1.65 42	0.16 4	2.20 56	0.16 4		

Metric table

Dimensions in: millimeters - inches

1			2			3											
l_1	d_1		l_2			d_3	d_4	h_1	h_2	h_3	h_4						
											Stroke						
120 4.72	M 10	M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	32 1.26	29.5 1.16	2 0.08	41.5 1.63	2.5 0.10		
145 5.71	M 12	M 16	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	23 0.91	40 1.57	42 1.65	4 0.16	56 2.20	4 0.16		

Specification

- Lever body
Zinc die-cast
- Powder coated
Black, RAL 9005, textured finish **● SW**
Silver, RAL 9006, textured finish **● SR**
- Hub cover
Plastic
- Black for SW
- Light gray for SR
- Countersunk screw
Stainless steel
- Chemically blackened finish for SW
- Plain finish for SR
- GN 126**
Threaded stud
Steel, blackened finish
- GN 126.1**
Threaded stud
Stainless steel AISI 303
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 126 and GN 126.1 flat adjustable tension levers are characterized by their low height and the timelessly elegant design.

They have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Adjustable Levers GN 300 (with Steel Tapped Insert) → page 402
- Adjustable Levers GN 300.1 (with Stainless Steel Tapped Insert) → page 406
- Adjustable Levers GN 300.5 (Stainless Steel, Matte Shot-Blasted Finish) → page 430
- Flat Adjustable Tension Levers GN 125 (with Steel Threaded Stud) → page 524
- Flat Adjustable Tension Levers GN 125.5 (Stainless Steel) → page 527

How to order (Inch, steel threaded stud)	1 Lever length l_1
	2 Thread d_1
GN 126-120-3/8X16-20-SW	3 Thread length l_2
	4 Color

How to order (Metric, stainless steel threaded stud)	1 Lever length l_1
	2 Thread d_1
GN 126.1-120-M10-40-SR	3 Thread length l_2
	4 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4