



- 1** Identification no.
- 2** With 4 stainless steel socket cap screws DIN 912

Metric table

Dimensions in: millimeters - inches

1 d_1 Bore	1 s_1 Square	2 d_2 Bore	2 s_2 Square	3 k_1 Clamping length	k_2 Clamping length	l_1	l_2	l_3	m	z_1 Screw locations for screw size	z_2 Screw locations for screw size	Accessory Recommended lever GN 911			
												for z_1 l_4			for z_2 l_4
B 30	V 30	B 40	V 40	60 2.36	76 2.99	120 4.72	79 3.11	98 3.86	55 2.17	M8-50	M10-55	63 2.48	78 3.07	78 3.07	92 3.62
B 30	V 30	B 50	V 50	60 2.36	76 2.99	120 4.72	79 3.11	98 3.86	55 2.17	M8-50	M10-55	63 2.48	78 3.07	78 3.07	92 3.62
B 40	V 40	B 50	V 50	60 2.36	76 2.99	120 4.72	79 3.11	98 3.86	55 2.17	M8-50	M10-55	63 2.48	78 3.07	78 3.07	92 3.62

Specification

- Body
Aluminum
 - Powder coated
Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted finish **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Adjustable levers GN 911 → page QVX

On request

- Other bore and square combinations d_1 / s_1 and d_2 / s_2

Information

The clamping bores of GN 135 two-way connector clamps are designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

The versions with square bores are also suitable for use with **profile systems**.

The bores and squares are arranged in such a way that an adaptation between different tube cross-sections is possible.

At the screw locations z_1 / z_2 , the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

see also...

- *Product Family Standard Parts for Profile Systems* → page QVX
- *Construction Tubes GN 990* → page QVX

How to order

GN 135-B30-V40-60-2-SW

1	Bore d_1 (Square s_1)
2	Square s_2 (Bore d_2)
3	Clamping length k_1
4	Identification no.
5	Finish