


Mounting holes - Outer slide




Metric table



Dimensions in: millimeters - inches

l_1	a_2	a_3	a_4	a_5
300 11.81	113.5 4.47	209.5 8.25	273.5 10.77	-
350 13.78	113.5 4.47	209.5 8.25	337.5 13.29	-
400 15.75	113.5 4.47	209.5 8.25	369.5 14.55	-
500 19.69	145.5 5.73	209.5 8.25	337.5 13.29	465.5 18.33

Mounting holes - Inner slide



Metric table



Dimensions in: millimeters - inches

l_1	i_3	i_4	i_5
300 11.81	142.5 5.61	182.5 7.19	-
350 13.78	167.5 6.59	207.5 8.17	-
400 15.75	192.5 7.58	232.5 9.15	282.5 11.12
500 19.69	242.5 9.55	282.5 11.12	357.5 14.07

Mounting screws

For the listed loading forces F_S to be absorbed reliably into the surrounding structure, all available through holes of the outer and inner slide must be used. Failure to use mounting screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - Standard		Outer slide	Inner slide
Phillips countersunk flat head screw	DIN 965	M 4	M 4
Phillips countersunk flat head self-tapping screw	DIN 7997	Size 3.5 / 4	Size 3.5

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

