



- 4 Identification no.**  
2 With 4 stainless steel socket cap screws DIN 912

**Metric table**

<b>1</b> <b>d<sub>1</sub> - d<sub>2</sub></b> Bore - Bore	<b>1</b> <b>d<sub>1</sub> - s<sub>2</sub></b> Bore - Square	<b>1</b> <b>s<sub>1</sub> - s<sub>2</sub></b> Square - Square	<b>2</b> <b>k</b> Clamping length	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>m</b>	<b>z</b> Screw locations for screw size	<b>Accessory</b> Recommended lever GN 911 for <b>z</b>	
								<b>l<sub>3</sub></b>	
B20 - B20	B20 - V20	V20 - V20	50 1.97	79.5 3.13	68 2.68	33.5 1.32	M8-30	63 2.48	78 3.07
B25 - B25	B25 - V25	V25 - V25	50 1.97	79.5 3.13	68 2.68	33.5 1.32	M8-30	63 2.48	78 3.07
B30 - B30	B30 - V30	V30 - V30	50 1.97	79.5 3.13	68 2.68	33.5 1.32	M8-30	63 2.48	78 3.07
B30 - B30	B30 - V30	V30 - V30	60 2.36	109 4.29	79 3.11	50 1.97	M8-50	63 2.48	78 3.07
B32 - B32	-	-	60 2.36	109 4.29	79 3.11	50 1.97	M8-50	63 2.48	78 3.07
B35 - B35	B35 - V35	V35 - V35	60 2.36	109 4.29	79 3.11	50 1.97	M8-50	63 2.48	78 3.07
B40 - B40	B40 - V40	V40 - V40	60 2.36	109 4.29	79 3.11	50 1.97	M8-50	63 2.48	78 3.07
B40 - B40	B40 - V40	V40 - V40	76 2.99	125 4.92	98 3.86	55 2.17	M10-50	78 3.07	92 3.62
B42 - B42	-	-	76 2.99	125 4.92	98 3.86	55 2.17	M10-50	78 3.07	92 3.62
B45 - B45	B45 - V45	V45 - V45	76 2.99	125 4.92	98 3.86	55 2.17	M10-50	78 3.07	92 3.62
B48 - B48	-	-	76 2.99	125 4.92	98 3.86	55 2.17	M10-50	78 3.07	92 3.62
B50 - B50	B50 - V50	V50 - V50	76 2.99	125 4.92	98 3.86	55 2.17	M10-50	78 3.07	92 3.62

Dimensions in: millimeters - inches

**Specification**

- Body  
Aluminum  
- Powder coated  
Black, RAL 9005, textured finish ● **SW**  
- Plain, matte shot-blasted finish ○ **BL**
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

**Accessory**

- Adjustable levers GN 911 → page 1810

**Information**

The clamping bores of GN 134 two-way connector clamps are not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

see also...

- [Product Family Standard Parts for Profile Systems](#) → page 18
- [Construction Tubes GN 990](#) → page 1836

How to order	
<b>1</b> Bore <b>d<sub>1</sub></b> - Square <b>s<sub>2</sub></b> ( <b>d<sub>1</sub></b> - <b>d<sub>2</sub></b> , <b>s<sub>1</sub></b> - <b>s<sub>2</sub></b> )	
<b>2</b> Clamping length <b>k</b>	
<b>3</b> Identification no.	
<b>4</b> Finish	

**GN 134-B45-V45-76-2-SW**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10