



- Identification no.**
2 With 6 stainless steel socket cap screws DIN 912

Metric table

Dimensions in: millimeters - inches

| d Bore | s Square | k Clamping length | l₁ | l₂ | l₃ | m | z Screw locations for screw size | Accessory Recommended lever GN 911 for z l₄ | |
|------------------|--------------------|-----------------------------|----------------------|----------------------|----------------------|---------------|--|--|------------|
| B 20 | V 20 | 50 1.97 | 172 6.77 | 68 2.68 | 46 1.81 | 86 3.39 | M8-35 | 63 2.48 | 78 3.07 |
| B 25 | V 25 | 50 1.97 | 172 6.77 | 68 2.68 | 46 1.81 | 86 3.39 | M8-35 | 63 2.48 | 78 3.07 |
| B 30 | V 30 | 50 1.97 | 172 6.77 | 68 2.68 | 46 1.81 | 86 3.39 | M8-35 | 63 2.48 | 78 3.07 |
| B 30 | V 30 | 60 2.36 | 203 7.99 | 79 3.11 | 59 2.32 | 101.5 4.00 | M8-50 | 63 2.48 | 78 3.07 |
| B 32 | - | 60 2.36 | 203 7.99 | 79 3.11 | 59 2.32 | 101.5 4.00 | M8-50 | 63 2.48 | 78 3.07 |
| B 35 | V 35 | 60 2.36 | 203 7.99 | 79 3.11 | 59 2.32 | 101.5 4.00 | M8-50 | 63 2.48 | 78 3.07 |
| B 40 | V 40 | 60 2.36 | 203 7.99 | 79 3.11 | 59 2.32 | 101.5 4.00 | M8-50 | 63 2.48 | 78 3.07 |
| B 40 | V 40 | 76 2.99 | 254 10.00 | 98 3.86 | 70 2.76 | 127 5.00 | M10-60 | 78 3.07 | 92 3.62 |
| B 42 | - | 76 2.99 | 254 10.00 | 98 3.86 | 70 2.76 | 127 5.00 | M10-60 | 78 3.07 | 92 3.62 |
| B 45 | V 45 | 76 2.99 | 254 10.00 | 98 3.86 | 70 2.76 | 127 5.00 | M10-60 | 78 3.07 | 92 3.62 |
| B 48 | - | 76 2.99 | 254 10.00 | 98 3.86 | 70 2.76 | 127 5.00 | M10-60 | 78 3.07 | 92 3.62 |
| B 50 | V 50 | 76 2.99 | 254 10.00 | 98 3.86 | 70 2.76 | 127 5.00 | M10-60 | 78 3.07 | 92 3.62 |

Specification

- Body
Aluminum
- Powder coated Black, RAL 9005, textured finish **SW**
- Plain, matte shot-blasted finish **BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Adjustable levers GN 911 → page QVX

Information

The clamping bores of GN 195 T-angle connector clamps are not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screw reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screw can be replaced by a GN 911 adjustable lever listed in the table as accessory.

see also...

- *Product Family Standard Parts for Profile Systems* → page QVX
- *Construction Tubes GN 990* → page QVX

| | |
|---------------------------|-----------------------------|
| How to order | 1 Square s (Bore d) |
| GN 195-V35-60-2-SW | 2 Clamping length k |
| | 3 Identification no. |
| | 4 Finish |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10