



SS Stainless Steel

4 Type

B With through holes

Metric table

² l ₁	² l ₃	² l ₄	³ l ₂	d ₁	d ₂	h	l ₅	l ₆	m ₁	m ₂	m ₃	s
70	105	140	50	6	6.5	12	35	70	42	30	39	3
2.76	4.13	5.51	1.97	0.24	0.26	0.47	1.38	2.76	1.65	1.18	1.54	0.12

Dimensions in: millimeters - inches

Specification

- Stainless steel AISI 304 Plain finish **NI**
- Pin Stainless steel AISI 304 Riveted **BL**
- Load Rating Information → page 2088
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Without bores
- With countersunk holes
- Other surface types

Information

GN 1364 stainless steel sheet metal hinges with wing and extended wing are characterized by their compact and universal dimensioning as well as their attractively shaped design. The materials used also permit applications in aggressive environments.

Type B is mounted with the existing through holes using screws or rivets.

see also...

- List of Hinge Types → page 1324
- Sheet Metal Hinges GN 136 (Steel or Stainless Steel) → page 1338 / 1339

<p>How to order</p> <p>¹ ² ³ ⁴ ⁵</p> <p>GN 1364-NI-70-50-B-BL</p>	1 Material
	2 Width l ₁ (Width l ₃ , Width l ₄)
	3 Length l ₂
	4 Type
	5 Finish

