


Metric




**5 Identification no.**

- 2 With 4 stainless steel socket cap screws ISO 4762



Socket cap screw / Hex nut



Adjustable lever GN 911

Metric table

Dimensions in: millimeters / inches

<b>d<sub>1</sub></b>	<b>s<sub>1</sub></b>	<b>d<sub>2</sub></b>	<b>s<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>k</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>m</b>	<b>t</b>	<b>x<sub>1</sub></b>	<b>x<sub>2</sub></b>	<b>y<sub>1</sub></b>	<b>y<sub>2</sub></b>	<b>Z<sub>1</sub></b>	<b>Z<sub>2</sub></b>	<b>Accessory I<sub>4</sub></b>	
Bore	Square	Bore	Square		Clamping length										Screw locations for screw size	Screw locations for screw size	Recom. lever GN 911 for z <sub>1</sub>	
B 20	V 20	B 20	V 20	6.5 0.26	50 1.97	86 3.39	30 1.18	68 2.68	33.5 1.32	7 0.28	75 2.95	60 2.36	50 1.97	35 1.38	M8-30	M8-35	63 2.48	78 3.07
B 25	V 25	B 25	V 25	6.5 0.26	50 1.97	86 3.39	30 1.18	68 2.68	33.5 1.32	7 0.28	75 2.95	60 2.36	50 1.97	35 1.38	M8-30	M8-35	63 2.48	78 3.07
B 30	V 30	B 30	V 30	6.5 0.26	50 1.97	86 3.39	30 1.18	68 2.68	33.5 1.32	7 0.28	75 2.95	60 2.36	50 1.97	35 1.38	M8-30	M8-35	63 2.48	78 3.07
B 40	V 40	B 40	V 40	11 0.43	76 2.99	136 5.35	46 1.81	98 3.86	55 2.17	14 0.55	115 4.53	90 3.54	76 2.99	50 1.97	M10-50	M10-50	78 3.07	92 3.62
B 42	-	B 42	-	11 0.43	76 2.99	136 5.35	46 1.81	98 3.86	55 2.17	14 0.55	115 4.53	90 3.54	76 2.99	50 1.97	M10-50	M10-50	78 3.07	92 3.62
B 45	V 45	B 45	V 45	11 0.43	76 2.99	136 5.35	46 1.81	98 3.86	55 2.17	14 0.55	115 4.53	90 3.54	76 2.99	50 1.97	M10-50	M10-50	78 3.07	92 3.62
B 48	-	B 48	-	11 0.43	76 2.99	136 5.35	46 1.81	98 3.86	55 2.17	14 0.55	115 4.53	90 3.54	76 2.99	50 1.97	M10-50	M10-50	78 3.07	92 3.62
B 50	V 50	B 50	V 50	11 0.43	76 2.99	136 5.35	46 1.81	98 3.86	55 2.17	14 0.55	115 4.53	90 3.54	76 2.99	50 1.97	M10-50	M10-50	78 3.07	92 3.62

**Specification**

**Connector clamp**

Aluminum

- Powder coated  
Black, RAL 9005, textured finish
- Plain finish, matte shot-blasted finish

- SW
- BL

**Socket cap screws ISO 4762**

Stainless steel A2

**Hex nuts DIN 985**

Stainless steel A2

Self-locking via polyamide ring

RoHS

**Technical Information**

Stainless Steel Characteristics QVX

**Accessory**

GN 911 Adjustable Levers QVX

The clamping bores of the flanged two-way connector clamps GN 141 are not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

The versions with square bores are also suitable for use with profile systems.

At the screw locations z<sub>1</sub> / z<sub>2</sub>, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws z<sub>1</sub> can be replaced by the adjustable levers GN 911 listed in the table as accessories.

see also...

GN 990 Construction Tubes (Aluminum / Stainless Steel)

Page

QVX

How to order

<b>1</b>	Square s <sub>1</sub> (Bore d <sub>1</sub> )
<b>2</b>	Bore d <sub>2</sub> (Square s <sub>2</sub> )
<b>3</b>	Identification no.
<b>4</b>	Finish

**GN 141-V50-B50-1-BL**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10