



- 3 Identification no.**
2 With 3 stainless steel socket cap screws DIN 912

Metric table

Dimensions in: millimeters - inches

1 d₁ Bore	2 d₂ Bore	d₃	d₄ Clamping thread	l₁	l₂	l₃	m	z Screw locations for screw size	Accessory Recommended lever GN 911 for z l₄	
B 20	B 20	40 1.57	M 8	120 4.72	80 3.15	52 2.05	60 2.36	M8-25	-	-
B 25	B 25	40 1.57	M 8	120 4.72	80 3.15	52 2.05	60 2.36	M8-25	78 3.07	-
B 30	B 30	40 1.57	M 8	120 4.72	80 3.15	52 2.05	60 2.36	M8-25	63 2.48	78 3.07
B 40	B 40	65 2.56	M 10	206 8.11	135.5 5.33	77.5 3.05	103 4.06	M10-50	-	-
B 42	B 42	65 2.56	M 10	206 8.11	135.5 5.33	77.5 3.05	103 4.06	M10-50	-	-
B 45	B 45	65 2.56	M 10	206 8.11	135.5 5.33	77.5 3.05	103 4.06	M10-50	92 3.62	-
B 48	B 48	65 2.56	M 10	206 8.11	135.5 5.33	77.5 3.05	103 4.06	M10-50	78 3.07	92 3.62
B 50	B 50	65 2.56	M 10	206 8.11	135.5 5.33	77.5 3.05	103 4.06	M10-50	78 3.07	92 3.62

Specification

- Body
Aluminum
- Powder coated
Black, RAL 9005, textured finish **● SW**
- Plain, Matte shot-blasted finish **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- Set screws DIN 914
Stainless steel AISI 304
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Adjustable levers GN 911 → page QVX

Information

The clamping bores of angle connector clamps GN 198 are designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable levers GN 911 listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → page QVX
- *Angle Connector Clamps GN 196* → page QVX

How to order

1 Bore d₁
2 Bore d₂
3 Identification no.
4 Finish

GN 198-B25-B25-2-SW

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10