


Mounting holes - Outer slide




Metric table

l_1	a_3	a_4	a_5	a_6
300 11.81	192 7.56	224 8.82	-	-
350 13.78	192 7.56	224 8.82	-	-
400 15.75	224 8.82	256 10.08	-	-
450 17.72	288 11.34	320 12.60	-	-
500 19.69	320 12.60	352 13.86	-	-
550 21.65	352 13.86	384 15.12	-	-

Dimensions in: millimeters - inches

l_1	a_3	a_4	a_5	a_6
600 23.62	416 16.38	448 17.64	-	-
700 27.56	448 17.64	480 18.90	-	-
800 31.50	384 15.12	416 16.38	672 26.46	704 27.72
900 35.43	416 16.38	448 17.64	768 30.24	800 31.50
1000 39.37	480 18.90	512 20.16	864 34.02	896 35.28
1200 47.24	576 22.68	608 23.94	1056 41.57	1088 42.83

Mounting holes - Inner slide



Metric table

l_1	i_2	i_3	i_4	i_5	i_6
300 11.81	150 5.91	280 11.02	-	-	-
350 13.78	175 6.89	330 12.99	-	-	-
400 15.75	200 7.87	380 14.96	-	-	-
450 17.72	225 8.86	430 16.93	-	-	-
500 19.69	250 9.84	480 18.90	-	-	-
550 21.65	275 10.83	530 20.87	-	-	-

Dimensions in: millimeters - inches

l_1	i_2	i_3	i_4	i_5	i_6
600 23.62	300 11.81	580 22.83	-	-	-
700 27.56	350 13.78	680 26.77	-	-	-
800 31.50	271 10.67	522.5 20.57	774 30.47	-	-
900 35.43	305 12.01	589 23.19	874 34.41	-	-
1000 39.37	258 10.16	497 19.57	735.5 28.96	974 38.35	-
1200 47.24	251 9.88	482 18.98	712 28.03	943 37.13	1174 46.22

Mounting screws

For the listed loading forces F_S to be absorbed reliably in the surrounding structure, all available countersunk holes of the outer and inner slide must be used. Failure to use mounting screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - Standard		Outer slide	Inner slide
Phillips countersunk flat head screw	DIN 965	M 5	M 4
Phillips countersunk flat head self-tapping screw	DIN 7997	Size 5	Size 4 / 4.5