


Inch | Metric



- 2 Bore code**
- B** Without keyway
 - K** With keyway
 - V** With square

Bore code



Metric table

1 d_1	3 d_2 Bore H7 Square H11	d_3	d_4	d_5	h_1	h_2	$h_3 \approx$	Length $l \approx$
50 1.97	12 0.472	28 1.10	8 0.31	20 0.79	26 1.02	9 0.35	53 2.09	82 3.23
55 2.17	14 0.551	30 1.18	10 0.39	25 0.98	28 1.10	10 0.39	61 2.40	96 3.78
60 2.36	15 0.591	32 1.26	10 0.39	25 0.98	30 1.18	11 0.43	64 2.52	96 3.78
65 2.56	16 0.630	35 1.38	12 0.47	30 1.18	32 1.26	12 0.47	71 2.80	110 4.33
72 2.83	18 0.709	40 1.57	12 0.47	32 1.26	36 1.42	14 0.55	80 3.15	124 4.88
80 3.15	20 0.787	44 1.73	14 0.55	35 1.38	40 1.57	16 0.63	89 3.50	138 5.43
100 3.94	24 0.945	54 2.13	16 0.63	40 1.57	52 2.05	24 0.94	113 4.45	170 6.69

Dimensions in: millimeters / inches

Specification

Hub / Shafts

Steel
Blackened finish

Ball knobs DIN 319

Plastic, phenolic resin (PF)
Black, shiny finish

RoHS

On request

- Special inch and metric bores, threads or keyways
- Other modifications such as set screw holes, cross holes, etc.

Four arm turret levers GN 213 are an excellent choice for applications where using a handwheel or crank handle is not practical.

Technical Information

Keyways WN 6885 / DIN 6885-1	Page QVX
Square Bores WN 79	Page QVX
ISO Fundamental Tolerances	Page QVX
Plastic Characteristics	Page QVX

How to order

1 Diameter d_1
2 Bore code
3 Bore d_2 (Keyway, Square)

GN213-65-B16

