


Metric



**elesa**  
Original design I.149

Metric table

Dimensions in: millimeters / inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub>	<b>3</b> l <sub>1</sub>	d <sub>3</sub>	l <sub>2</sub> min.	l <sub>3</sub> ±0.5	l <sub>4</sub> ≈
34 1.34	M 10	67 2.64	19 0.75	40 1.57	8 0.31	24 0.94
34 1.34	M 10	86 3.39	20 0.79	48 1.89	7 0.28	25 0.98

**Specification**

Plastic, Phenolic (PF)

- Operating temperature  
-4 °F to +230 °F (-20 °C to +110 °C)
- Black, shiny finish

RoHS

When using tapered knobs EN 219, make sure that the threaded end of the shaft is long enough and seats flush inside the threaded hole of the handle, otherwise the plastic may break under excessive stress.

**Technical Information**

Plastic Characteristics

Page

QVX

How to order

**EN 219-34-M10-67**

- 1** Handle diameter d<sub>1</sub>
- 2** Thread d<sub>2</sub>
- 3** Handle length l<sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

