


Mounting holes - Outer slide




Metric table

Dimensions in: millimeters - inches

l_1	a_1	a_2
500 19.69	64 2.52	192 7.56
600 23.62	80 3.15	240 9.45
700 27.56	96 3.78	288 11.34
800 31.50	112 4.41	336 13.23

Mounting holes - Inner slide



Metric table

Dimensions in: millimeters - inches

l_1	i_1	i_2
500 19.69	64 2.52	192 7.56
600 23.62	80 3.15	240 9.45
700 27.56	96 3.78	288 11.34
800 31.50	112 4.41	336 13.23

Mounting screws

For the listed loading forces F_S to be absorbed reliably in the surrounding structure, all available countersunk holes of the outer and inner slide must be used. Failure to use mounting screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - Standard		Outer slide	Inner slide
Phillips countersunk flat head screw	DIN 965	M 5	M 4
Phillips countersunk flat head self-tapping screw	DIN 7997	Size 5	Size 4 / 4.5