



Metric

2 Type

- A** For two-hole flange
($d_1 = 60 / 90 / 113$ mm)
- B** For four-hole flange
($d_1 = 113 / 126$ mm)

Metric table

Dimensions in: millimeters - inches

d_1 Ø Leveling foot GN 148	1 l_1 Type A	1 l_2 Type B	d_2 Type A	d_3	m_1 Type A	m_2 Type B	s
60 2.36	128 5.04	-	78 3.07	65 2.56	110 4.33	-	3 0.12
90 3.54	170 6.69	-	110 4.33	90 3.54	140 5.51	-	3 0.12
113 4.45	216 8.50	168 6.61	150 5.91	120 4.72	184 7.24	132 5.20	4 0.16
126 4.96	-	184 7.24	-	150 5.91	-	150 5.91	4 0.16

Specification

- Rubber pad
Perbunan® (NBR) 68 ±5 shore A
- Black
- Oil resistant
- *Elastomer Characteristics* → page QVX
- **RoHS compliant**

Information

GN 148.2 rubber pads are used on GN 148 vibration damping leveling feet for installing machines where no firm bolt connection to the ground is intended.

To attach to leveling foot, snap into the attachment bore holes of the flanges. Small bumps at the bottom face of the rubber pads enhance stability.

see also...

- *Vibration Damping Leveling Feet GN 148* → page QVX

<p>How to order</p> <p>GN 148.2-168-B</p>	1 Length l_2 (Length l_1)
	2 Type