



**Metric table**

Dimensions in: millimeters - inches

d Bore	l <sub>1</sub>	l <sub>2</sub>	m <sub>1</sub>	m <sub>2</sub>	s <sub>1</sub> Square	t ≈	x	y <sub>1</sub>	y <sub>2</sub>
B 10	40 1.57	21 0.83	20 0.79	4.5 0.18	V 8	10 0.39	30 1.18	56 2.20	40 1.57
B 12	40 1.57	21 0.83	20 0.79	4.5 0.18	V 10	10 0.39	30 1.18	56 2.20	40 1.57
B 14	40 1.57	21 0.83	20 0.79	4.5 0.18	V 12	10 0.39	30 1.18	56 2.20	40 1.57

**Specification**

- Body  
Plastic  
Technopolymer (Polyamide)  
- Glass fiber reinforced  
- Temperature resistant up to 140 °F (60 °C)  
- Black, matte finish
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts ISO 4032  
Stainless steel AISI 304
- *Plastic Characteristics* → page XYZ
- *Stainless Steel Characteristics* → page XYZ
- **RoHS compliant**

**Information**

- see also...
- *Product Family Standard Parts for Profile Systems* → page XYZ
  - *Base Plate Mounting Clamps GN 473 (Aluminum)* → page XYZ
  - *Rods / Tubes GN 480.1* → page XYZ
  - *Work Gripper Block EN 176* → page XYZ
  - *T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems)* → page XYZ
  - *T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems)* → page XYZ

How to order	1 Bore d
<b>EN 175-B12</b>	

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

