



- 2** Identification no.
2 With 2 stainless steel socket cap screws ISO 4762

Metric table

Dimensions in: millimeters - inches

1 d Bore	1 s Square	2 k Clamping length	1 l ₁	1 l ₂	1 l ₃	1 z Screw locations for screw size	Accessory Recommended lever GN 911 for z l ₄	
B 20	V 20	50 1.97	68 2.68	46 1.81	48 1.89	M8-35	63 2.48	78 3.07
B 25	V 25	50 1.97	68 2.68	46 1.81	48 1.89	M8-35	63 2.48	78 3.07
B 30	V 30	50 1.97	68 2.68	46 1.81	48 1.89	M8-35	63 2.48	78 3.07
B 30	V 30	60 2.36	79 3.11	59 2.32	58 2.28	M8-50	63 2.48	78 3.07
B 32	-	60 2.36	79 3.11	59 2.32	58 2.28	M8-50	63 2.48	78 3.07
B 35	V 35	60 2.36	79 3.11	59 2.32	58 2.28	M8-50	63 2.48	78 3.07
B 40	V 40	60 2.36	79 3.11	59 2.32	58 2.28	M8-50	63 2.48	78 3.07
B 40	V 40	76 2.99	98 3.86	70 2.76	73 2.87	M10-60	78 3.07	92 3.62
B 42	-	76 2.99	98 3.86	70 2.76	73 2.87	M10-60	78 3.07	92 3.62
B 45	V 45	76 2.99	98 3.86	70 2.76	73 2.87	M10-60	78 3.07	92 3.62
B 48	-	76 2.99	98 3.86	70 2.76	73 2.87	M10-60	78 3.07	92 3.62
B 50	V 50	76 2.99	98 3.86	70 2.76	73 2.87	M10-60	78 3.07	92 3.62
B 60	V 60	90 3.54	108.5 4.27	84 3.31	83 3.28	M10-75	-	-

Specification

- Connector Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Plain, matte shot-blasted finish
- Socket cap screws ISO 4762
Stainless steel A2
- Hex nuts DIN 985
Stainless steel AISI A2
Self-locking via polyamide ring
- RoHS compliant



Information

The clamping bore of GN 241 tube connectors is not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

How to order

GN 241-V45-76-2-SW

1	Square s (Bore d)
2	Clamping length k
3	Identification no.
4	Finish