


Metric table



Dimensions in: millimeters - inches

d ₁	d ₂	d ₃	d ₄	b	h	Part number hook spanner wrench 
M 12 x 1.5	28 <i>1.10</i>	23 <i>0.91</i>	M 4	5 <i>0.20</i>	6 <i>0.24</i>	DIN 1810-A25-28
M 14 x 1.5	30 <i>1.18</i>	25 <i>0.98</i>	M 4	5 <i>0.20</i>	7 <i>0.28</i>	DIN 1810-A30-32
M 16 x 1.5	32 <i>1.26</i>	27 <i>1.06</i>	M 5	5 <i>0.20</i>	7 <i>0.28</i>	DIN 1810-A30-32
M 18 x 1.5	34 <i>1.34</i>	28 <i>1.10</i>	M 5	6 <i>0.24</i>	8 <i>0.31</i>	DIN 1810-A34-36
M 20 x 1.5	36 <i>1.42</i>	30 <i>1.18</i>	M 5	6 <i>0.24</i>	8 <i>0.31</i>	DIN 1810-A34-36
M 22 x 1.5	40 <i>1.57</i>	34 <i>1.34</i>	M 5	6 <i>0.24</i>	9 <i>0.35</i>	DIN 1810-A40-42
M 24 x 1.5	42 <i>1.65</i>	36 <i>1.42</i>	M 5	6 <i>0.24</i>	9 <i>0.35</i>	DIN 1810-A40-42
M 30 x 1.5	50 <i>1.97</i>	43 <i>1.69</i>	M 5	7 <i>0.28</i>	10 <i>0.39</i>	DIN 1810-A45-50
M 35 x 1.5	55 <i>2.17</i>	48 <i>1.89</i>	M 6	7 <i>0.28</i>	11 <i>0.43</i>	DIN 1810-A52-55
M 40 x 1.5	62 <i>2.44</i>	54 <i>2.13</i>	M 8	8 <i>0.31</i>	12 <i>0.47</i>	DIN 1810-A58-62

Specification

- Nut
Steel
- Property class 5
- Blackened finish
- Set screw
Steel, blackened finish
- Strength Values of Nuts → page 2127
- RoHS compliant



ST

Information

GN 1804.2 slotted spanner lock nuts with thread locking can be secured against twisting via the d₄ set screw. The thread flanks of the nut ensure damage-free securing and can be used as often as needed. The offset smooth surface d₃ is intended as an axial contact surface.

see also...

- Slotted Spanner Nuts DIN 1804 (Steel / Stainless Steel) → page XYZ
- Slotted Spanner Lock Nuts GN 1804.1 (Self-Locking) → page XYZ
- Slotted Spanner Nuts DIN 70852 (Flat Design) → page XYZ

Accessory

- Hook spanner wrenches DIN 1810
(Part number, see table)

How to order	1 Thread d ₁
	2 Material

GN 1804.2-M20X1.5-ST

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

