



SS Stainless Steel

3 Type

- A** Without seals
- B** With seals

4 Identification no.

- 4** With 2 stainless steel cap nuts DIN 917

Metric table

Dimensions in: millimeters - inches

1 d₁ Bore with sleeve bearing	2 d₂ Bore	b	d₃ Mounting screws on the drive key	k₁ Clamping length	k₂ Clamping length	l₁	l₂	m	z₁ Screw location for screw size	z₂ Screw location for screw size	Accessory Recommended lever GN 911.3			
											for z₁ l₃		for z₂ l₃	
G 30	B 30	22 0.87	M 4	37 1.46	42 1.65	96 3.78	35 1.38	60 2.36	M 8	M 8	63 2.48	78 3.07	63 2.48	78 3.07
G 50	B 50	30 1.18	M 6	65 2.56	75 2.95	151.5 5.96	48.5 1.91	103 4.06	M 10	M 10	78 3.07	92 3.62	78 3.07	92 3.62

Specification

- Body
Stainless steel AISI CF-8
Matte shot-blasted
- Sleeve bearing
Plastic (PTFE)
- Carriage bolt DIN 603
Stainless steel A2
- Cap nuts DIN 917 / washers
Stainless steel A2
- Seals
 - Sealing disks
Plastic (Polyacetal POM)
 - Spacer ring
Silicon, 40 ... 60 shore A
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Adjustable levers GN 911.3 → page QVX

Information

T-angle linear actuator connectors GN 192.15 are based on T-angle connector clamps. The additionally provided mounting holes are used to connect to the drive key of a linear actuator. Bores with the designation "G" are equipped with sleeve bearings.

With the screw locations **z₂**, the play of the guide bore **d₁** can be adjusted or the linear actuator connectors can be clamped after adjustment. Type B is equipped with seals at the screw locations.

For quick clamping without tools, the cap nuts can be replaced by the adjustable levers GN 911.3 listed in the table as accessories.

see also...

- *Linear Actuators GN 291* → page QVX
- *Linear Actuators GN 292* → page QVX
- *Linear Actuators GN 293* → page QVX

How to order	1 Bore d₁
	2 Bore d₂
	3 Type
	4 Identification no.
GN 192.15-G50-B50-A-4	