



Metric table

Dimensions in: millimeters - inches

h	b ±0.1	For GN 614				For GN 615 / GN 615.2 / GN 615.3			
		Size	d	w	s min.	Size	d	w	s min.
8.5 0.33	3.4 0.13	6 0.24	5 0.20	1.6 0.06	0.9 0.04	M 8	4.5 0.18	1.5 0.06	0.8 0.03
10.5 0.41	4.5 0.18	8 0.31	6.5 0.26	1.9 0.07	1 0.04	M 10	6 0.24	2 0.08	1 0.04

Specification

- Positioning block
- Sintered steel
- Case hardened
- Plain finish
- **RoHS compliant**

Information

GN 250 positioning blocks are used together with ball plungers as a detent for the positioning of slides, covers and similar applications.

see also...

- *Short Press-Fit Ball Plungers GN 614 → page QVX*
- *Ball Plungers GN 615 → page QVX*
- *Ball Plungers GN 615.2 → page QVX*
- *Ball Plungers GN 615.3 → page QVX*
- *Holding Blocks GN 614.1 → page QVX*

How to order	1	Height h
GN 250-8.5		

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10