



SS Stainless Steel

3 Type

- A Without seals
- B With seals

4 Identification no.

- 4 With 2 stainless steel cap nuts DIN 917

Metric table

Dimensions in: millimeters - inches

d ₁ Bore	d ₂ Bore	b	k ₁ Clamping length	k ₂ Clamping length	l ₁	l ₂	m	z ₁ Screw location for screw size	z ₂ Screw location for screw size	Accessory Recommended lever GN 911.3			
										for z ₁ l ₃		for z ₂ l ₃	
B 30	B 30	22 0.87	37 1.46	42 1.65	96 3.78	35 1.38	60 2.36	M 8	M 8	63 2.48	78 3.07	63 2.48	78 3.07
B 50	B 50	30 1.18	65 2.56	75 2.95	151.5 5.96	48.5 1.91	103 4.06	M 10	M 10	78 3.07	92 3.62	78 3.07	92 3.62

Specification

- Body
Stainless steel AISI CF-8
Matte shot-blasted finish
- Carriage bolts DIN 603
Stainless steel A2
- Cap nuts DIN 917 / washers
Stainless steel A2
- Seals
 - Sealing disks
Plastic (Polyacetal POM)
 - Spacer ring
Silicone, 40 ... 60 shore A
- [Plastic Characteristics](#) → page QVX
- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

Accessory

- Adjustable levers GN 911.3 → page QVX

Information

The clamping bores of GN 192.5 T-angle connector clamps are mechanically machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw locations z₁ / z₂, the carriage bolts and cap nuts reduce the bore cross-section for clamping. Type B is equipped with seals at the screw locations.

For clamping without tools, the cap nuts can be replaced by the GN 911.3 adjustable levers listed in the table as accessories.

see also...

- [Construction Tubes GN 990](#) → page QVX

How to order

GN 192.5-B30-B30-A-4

1	Bore d ₁
2	Bore d ₂
3	Type
4	Identification no.