



Inch | Metric



**SS** Stainless Steel

**Specification**

**Crank body**

Stainless steel precision casting AISI CF-8  
Contact face of hub machined

**Revolving handle** similar to GN 598.1

- Plastic, phenolic resin (PF)
- Black, shiny finish
- Spindle
- Stainless steel AISI 304

RoHS

**On request**

- Other modifications such as special inch and metric bores, keyways, set screw holes, etc.
- With retractable handle GN 798.5

Straight crank handles GN 269 have been designed to comply with stringent hygiene requirements.

The cylindrical handles are made of phenolic resin material, which provides good resistance to chemicals.

**Technical Information**

	Page
Cross Holes GN 110	QVX
Square Bores WN 79	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order (Inch)

**GN 269-80-B1/2**

1 Length l

2 Bore d<sub>1</sub>

How to order (Metric)

**GN 269-125-V14**

1 Length l

2 Square s (Bore d<sub>1</sub>)

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4



## Inch table

1

2

Dimensions in: inches / millimeters

Length l	d <sub>1</sub> H9 Bore	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	h <sub>3</sub>	h <sub>4</sub> ≈	Ø Handle
3.15 80	B 1/2	0.87 22	0.87 22	0.61 15.4	0.26 6.6	1.77 45	0.71 18
3.94 100	B 1/2	1.02 26	1.02 26	0.70 17.7	0.33 8.3	2.17 55	0.83 21
4.92 125	B 5/8	1.10 28	1.10 28	0.74 18.8	0.36 9.2	2.80 71	0.91 23
6.30 160	B 3/4	1.26 32	1.26 32	0.89 22.6	0.37 9.4	2.80 71	0.91 23

## Metric table

1

2

2

Dimensions in: millimeters / inches

Length l	d <sub>1</sub> H9 Bore	s H11 Square	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	h <sub>3</sub>	h <sub>4</sub> ≈	Ø Handle
80 3.15	B 10	V 10	22 0.87	22 0.87	15.4 0.61	6.6 0.26	45 1.77	18 0.71
100 3.94	B 12	V 12	26 1.02	26 1.02	17.7 0.70	8.3 0.33	55 2.17	21 0.83
125 4.92	B 14	V 14	28 1.10	28 1.10	18.8 0.74	9.2 0.36	71 2.80	23 0.91
160 6.30	B 17	V 17	32 1.26	32 1.26	22.6 0.89	9.4 0.37	71 2.80	23 0.91
200 7.87	B 19	V 19	38 1.50	38 1.50	28 1.10	9.4 0.37	71 2.80	23 0.91