



Type OZ

Type AV



Metric



elesa

Original design TCC-PB / TCC-PBF



3 Type

OZ Without centering step (smooth)

AV With external serration

Metric table

Dimensions in: millimeters / inches

b	x ₁	d ₁	d ₂	Length l	m ₁	m ₂	t ₁	t ₂	s	x ₂	y ₁	y ₂
40 1.57	40 1.57	8.5 0.33	6.5 0.26	54 2.13	33 1.30	20 0.79	-	8 0.31	13.5 0.53	-	75 2.95	60 2.36
40 1.57	75 2.95	8.5 0.33	6.5 0.26	54 2.13	33 1.30	37.5 1.48	30 1.18	8 0.31	13.5 0.53	60 2.36	75 2.95	60 2.36

Specification

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature
-4 °F to +212 °F (-20 °C to +100 °C)
- Color
- Black, RAL 9005, matte finish
- Gray, RAL 7040, matte finish

- SW
- GR

RoHS

The fixing lug of the swivel clamp connector bases EN 272.9 is available with a smooth surface or with external serration.

The flange with two or four bores serves for fastening the clamp connector. Swivel clamp connector bases EN 272.9 can be assembled with swivel clamp connectors EN 276.9 and EN 278.9 to create swivel clamp connector joints.

see also...

	Page
EN 282.9 Swivel Clamp Connector Joints	QVX
EN 276.9 Swivel Clamp Connectors	QVX
EN 278.9 Swivel Clamp Connectors	QVX
GN 272 Swivel Clamp Connector Bases	QVX

Technical Information

Plastic Characteristics

QVX

How to order

EN 272.9-40-75-OZ-SW

- Swivel width b
- Length x₁
- Type
- Color

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10