



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	a	b	h <sub>1</sub>	h <sub>2</sub> ≈	Length l ≈
16 0.63	M 8	7 0.28	12 0.47	12 0.47	35 1.38	56 2.20
20 0.79	M 10	9 0.35	14 0.55	14 0.55	44 1.73	70 2.76
25 0.98	M 12	11 0.43	18 0.71	18 0.71	52 2.05	87 3.43
32 1.26	M 16	15 0.59	22 0.87	22 0.87	66 2.60	109 4.29
40 1.57	M 20	18 0.71	28 1.10	28 1.10	84 3.31	140 5.51

**Specification**

- Malleable iron —
- Fettled
- Contact faces machined
- Stainless steel precision casting **NI**
- AISI CF-8
- Fettled
- Contact faces machined
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

**Information**

GN 206 clamp nuts are simple components. The stainless steel version is a good choice for certain corrosion free environment applications.

see also...

- *Clamp Nuts GN 99.5 (Steel, Zinc Plated)* → page QVX
- *Clamp Nuts GN 99.6 (Stainless Steel)* → page QVX

**On request**

- Clamp nuts GN 206, powder coated
- Special inch and metric bores or threads

How to order (Malleable Iron)	<sup>1</sup> <sup>2</sup>	1 Diameter d <sub>1</sub>
	<b>GN 206-32-M16</b>	2 Thread d <sub>2</sub>

How to order (Stainless steel)	<sup>1</sup> <sup>2</sup> <sup>3</sup>	1 Diameter d <sub>1</sub>
	<b>GN 206-25-M12-NI</b>	2 Thread d <sub>2</sub>
		3 Material