



- 3 Identification no.**
2 With stainless steel socket cap screw DIN 912

Metric table

Dimensions in: millimeters - inches

1 d ₁ Bore for clamping Ø	2 d ₂ Bore for sensor	b Swivel width	d ₃	k	l ₁	m	t	z Screw location for screw size	Accessory Recommended lever GN 911 for z l ₂		
B 12	B 12	B 18	25 0.98	27 1.06	25 0.98	64 2.52	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 14	B 12	B 18	25 0.98	27 1.06	25 0.98	64 2.52	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 15	B 12	B 18	25 0.98	27 1.06	25 0.98	64 2.52	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 16	B 12	B 18	25 0.98	27 1.06	25 0.98	64 2.52	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 18	B 12	B 18	25 0.98	27 1.06	25 0.98	64 2.52	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48

Specification

- Body
Aluminum
Powder coated
Black, RAL 9005, textured finish **SW**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

The clamping bore of GN 273.4 sensor holders is mechanically machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw location z, the socket cap screw reduces the bore cross-section for clamping.

For clamping without tools, the socket cap screw can be replaced by a GN 911 adjustable lever listed in the table as accessory.

see also...

- *Construction Tubes GN 990* → page 1836
- *Rods / Tubes GN 480.1* → page 1838
- *Attachment Mounting Clamps GN 478* → page 1827
- *Sensor Holders GN 271.4* → www.jwwinco.com

Accessory

- Adjustable levers GN 911 → page 1810

On request

- Stainless steel version

How to order	1 Bore d ₁
1 2 3 4	2 Bore d ₂
GN 273.4-B14-B18-2-SW	3 Identification no.
	4 Finish

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10