



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	a	b	h ₁	h ₂ ≈	Length l ≈
16 0.63	M 8	7 0.28	12 0.47	12 0.47	36 1.42	56 2.20
20 0.79	M 10	9 0.35	14 0.55	14 0.55	44.5 1.75	70 2.76
25 0.98	M 12	11 0.43	18 0.71	18 0.71	55 2.17	87 3.43
32 1.26	M 16	15 0.59	22 0.87	22 0.87	68.5 2.70	109 4.29
40 1.57	M 20	18 0.71	28 1.10	28 1.10	87 3.43	140 5.51

Specification

- Malleable iron —
- Fettleed
- Contact faces machined
- Stainless steel precision casting AISI CF-8 **NI**
- Fettleed
- Contact faces machined
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

- GN 206.1 double arm clamp nuts are solid components. The stainless steel version is a good choice for certain corrosion free environment applications.
- see also...
- *Double Arm Clamp Nuts GN 99.7 (Steel, Zinc Plated)* → page 545
 - *Double Arm Clamp Nuts GN 99.8 (Stainless Steel)* → page 545

On request

- Double arm clamp nuts GN 206.1, powder coated
- Special inch and metric bores or threads

How to order (Steel) ¹ ² GN 206.1-32-M16	1 Diameter d ₁
	2 Thread d ₂
How to order (Stainless steel) ¹ ² ³ GN 206.1-20-M10-NI	1 Diameter d ₁
	2 Thread d ₂
	3 Material