



3 Type

- C** Angled lever, with plain bore, tol. H7
- E** Angled lever, with tapped bore
- B** Straight lever, with plain bore, tol. H7
- D** Straight lever, with tapped bore

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread		d ₃ H7 Bore		d ₄	d ₅	h ₁	h ₂ ≈		l ₁ ≈		l ₂ ≈	t ₁ min.	t ₂ min.
	Type E	Type D	Type C	Type B				Type C Type E	Type B Type D	Type C Type E	Type B Type D			
22 0.87	M 10	M 10	B 10	B 10	8 0.31	20 0.79	37 1.46	67 2.64	40.5 1.59	89.5 3.52	96 3.78	85 3.35	15 0.59	19 0.75
25 0.98	M 12	M 12	B 12	B 12	10 0.39	25 0.98	42 1.65	76 2.99	47 1.85	100.5 3.96	107.5 4.23	95 3.74	18 0.71	21 0.83
28 1.10	M 12	M 12	B 12	B 12	12 0.47	30 1.18	47 1.85	87 3.43	53 2.09	114 4.49	122 4.80	108 4.25	18 0.71	23 0.91
32 1.26	M 16	M 16*	B 16	B 16*	12 0.47	32 1.26	52 2.05	98 3.86	59 2.32	133 5.24	142 5.59	126 4.96	23 0.91	28 1.10
36 1.42	M 16	M 16	B 16	B 16*	14 0.55	35 1.38	58 2.28	108 4.25	64.5 2.54	146 5.75	156 6.14	138 5.43	24 0.94	28 1.10
40 1.57	M 20	M 20*	B 20	B 20	16 0.63	40 1.57	64 2.52	120 4.72	72 2.83	162.5 6.40	174 6.85	154 6.06	27 1.06	30 1.18

* Not available from stock, requires a minimum order quantity

Specification

- Hub / lever
Steel, blackened finish
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Cross Holes GN 110 → page 2042
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

On request

- Special bores, threads, and threaded studs

Information

GN 212 tension levers are used as clamping devices as well as operating levers.

see also...

- Heavy Duty Adjustable Levers GN 212.3 (Steel, Blackened Finish) → page 517
- Heavy Duty Adjustable Levers GN 212.5 (Stainless Steel) → page 520

<p>How to order</p> <p>GN 212-28-B12-C</p>	1	Diameter d ₁
	2	Bore d ₃ (Thread d ₂)
	3	Type