



Inch | Metric



Inch table

Dimensions in: inches / millimeters

<sup>2</sup> d <sub>1</sub>	<sup>3</sup> d <sub>2</sub> Thread		<sup>3</sup> d <sub>3</sub> H7 Bore			d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>
1.97 50	5/16 x 18	3/8 x 16	B 5/16	B 3/8	Blank	0.71 18	0.98 25	0.79 20	0.59 15
2.48 63	3/8 x 16	1/2 x 13	B 3/8	B 1/2	Blank	0.79 20	1.18 30	0.94 24	0.71 18
3.15 80	5/8 x 11	-	B 1/2	B 5/8	Blank	0.98 25	1.42 36	1.14 29	0.87 22

Metric table

Dimensions in: millimeters / inches

<sup>2</sup> d <sub>1</sub>	<sup>3</sup> d <sub>2</sub> Thread		<sup>3</sup> d <sub>3</sub> H7 Bore			d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>
50 1.97	M 8	M 10	B 8	B 10		18 0.71	25 0.98	20 0.79	15 0.59
63 2.48	M 10	M 12	B 10	B 12		20 0.79	30 1.18	24 0.94	18 0.71
80 3.15	M 16	-	B 12	B 16		25 0.98	36 1.42	29 1.14	22 0.87

Specification

Plastic, Polyamide (PA)

- Shock-resistant
- Black, matte finish
- Hub bushing
- Steel, blackened finish

RoHS

On request

- Other modifications such as special inch and metric bores, keyways, set screw holes and other handle types etc.
- Without bore

<sup>1</sup> KT

Knurled control knobs GN 226 are mainly used instead of star and hand knobs for light adjusting or clamping applications.

Cover disks GN 226.1 widen the range of applications for these knurled handwheels.

see also...

EN 534 Diamond Cut Knurled Knobs (Plastic)

Page

QVX

Technical Information

Cross Holes GN 110

ISO Fundamental Tolerances

Plastic Characteristics

QVX

QVX

QVX

Accessory

GN 226.1 Cover Disks

GN 826 Control Knob Flanges (for Adjustable Spindles)

QVX

QVX

How to order

**GN 226-KT-50-M10**

<sup>1</sup>	Material
<sup>2</sup>	Knob diameter d <sub>1</sub>
<sup>3</sup>	Thread d <sub>2</sub> (Bore diameter d <sub>3</sub> )

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

