



Metric table

Dimensions in: millimeters - inches

1	2	3						d ₃	d ₄	h ₁	h ₃	h ₄ Stroke
63 2.48	M 6	20 0.79	27 1.06	-	-	-	24 0.94	17.5 0.69	34.5 1.36	48.5 1.91	4 0.16	
78 3.07	M 8	21 0.83	36 1.42	-	-	-	25 0.98	21 0.83	39.5 1.56	58.5 2.30	4 0.16	
92 3.62	M 10	29 1.14	47 1.85	-	-	-	30 1.18	24 0.94	46.5 1.83	68.5 2.70	4 0.16	
108 4.25	M 12	34 1.34	50 1.97	57 2.24	65 2.56	85 3.35	35 1.38	30 1.18	56.5 2.22	82 3.23	5 0.20	

Specification

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Orange, RAL 2004, textured finish ● **OS**
 - Red, RAL 3000, textured finish ● **RS**
 - Silver, RAL 9006, textured finish ● **SR**
- Chrome plated finish ● **CR**
- Threaded stud
Steel
 - Nitrided, blackened finish
 - Property class 5.8
- Axial bearing / retaining screw
Steel, blackened finish
- Strength Values of Screws → page 2127
- RoHS compliant

On request

- Black, RAL 9005, silk shiny finish ● **SZ**

Information

An extension of the GN 300 version, the GN 300.4 adjustable levers function the same as normal adjustable levers, but are produced with a clamping area which is linked via an axial bearing to the insert and screw of the adjustable lever.

This design creates a clamping force that is doubled through vastly reduced friction. There is no movement on the contact area between the lever and component, greatly reducing any marring of the surface of the clamping area. The increased clamping force also results in a reduced creep factor.

How to order	
1	Lever length l ₁
2	Thread d ₁
3	Thread length l ₂
4	Color (Finish)

GN300.4-92-M10-47-RS

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4