



Metric



4 Sensitivity

30 Angular minutes, bubble moves by 2 mm

Metric table

2

Dimensions in: millimeters / inches

d ₁	d ₂	d ₃ -0.2	h ₁	h ₂
20 0.79	12 0.47	18 0.709	10 0.39	8 0.31
25 0.98	14 0.55	20 0.787	12 0.47	9 0.35
30 1.18	20 0.79	28 1.102	13 0.51	10 0.39

Specification

1 3

Housing

Aluminum

- Anodized finish, natural color
- Anodized finish, black

● ALN
● ALS

Spirit level element

- Glass plastic body
- Filling
- Colorless-transparent

K

Casting compound

Mineral-based

RoHS

On request

- Green transparent filling
- Other sensitivities
- Brass or stainless steel housing

Bull's eye spirit levels GN 2278 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The housing is grooved at its lower diameter d₃, making it easier to install into the mating bore hole, e.g. by gluing.

The spirit levels are aligned in relation to the reference or contact surface, so that the bubble is located inside the marking ring once the horizontal position of the contact surface is reached.

see also...

	Page
GN 2277 Bull's Eye Spirit Levels (with Mounting Flange)	QVX
GN 2281 Bull's Eye Spirit Levels (for Installation in Plates and Housings)	QVX
GN 2279 Bull's Eye Spirit Levels (for Surface Mounting)	QVX
GN 2280 Bull's Eye Spirit Levels (Adjustable)	QVX
GN 2282 Screw-On Spirit Levels (with Mounting Holes)	QVX

Technical Information

General Information on Bull's Eye, Screw-On and Cross Spirit Levels QVX

How to order

1	Color
2	Outside diameter d ₁
3	Filling
4	Sensitivity

GN 2278-ALS-25-K-30

1.1
1.2
1.3
1.4

2.1
2.2
2.3
2.4

