


Spindle square



Metric



Metric table

Dimensions in: millimeters / inches

d	S ₀ Square	S ₁ ±0.1	S ₂ ±0.1	l ₁ ±0.5	l ₂	No. of spokes
50 1.97	V 6	5.9 0.232	6.15 0.242	8.5 0.33	12 0.47	3
50 1.97	V 7	6.9 0.272	7.15 0.281	8.5 0.33	12 0.47	3
60 2.36	V 6	5.9 0.232	6.15 0.242	8.5 0.33	12 0.47	3
60 2.36	V 7	6.9 0.272	7.15 0.281	8.5 0.33	12 0.47	3
70 2.76	V 7	6.9 0.272	7.15 0.281	10 0.39	15 0.59	3
70 2.76	V 8	7.9 0.311	8.15 0.321	10 0.39	15 0.59	3
80 3.15	V 8	7.9 0.311	8.15 0.321	11 0.43	16 0.63	3
80 3.15	V 9	8.9 0.350	9.15 0.360	11 0.43	16 0.63	3
90 3.54	V 9	8.9 0.350	9.15 0.360	11 0.43	16 0.63	3
100 3.94	V 9	8.9 0.350	9.15 0.360	13 0.51	20 0.79	3
100 3.94	V 10	9.9 0.390	10.15 0.400	13 0.51	20 0.79	3
130 5.12	V 12	11.9 0.469	12.15 0.478	15 0.59	23 0.91	3

Specification

Steel sheet metal

ST

- Powder coated
 - Black, RAL 9005, matte finish
 - Red, RAL 3000, matte finish
- Zinc plated, blue passivated finish

- SW
- RT
- ZB

RoHS

Valve handwheels GN 227.6 have been specially developed for valves and they offer definite advantages:

They consist of a single unwelded piece of steel sheet metal manufactured by a special process to give a reinforced hub. They offer high mechanical strength and are not affected by shocks and knocks.

They are resistant to temperature and fire and not weakened by any aging process.

The slightly tapered square hole allows easy installation and firm seating on a spindle.

They are of an attractive design and low cost.

see also...

GN 227.7 Valve Handwheels (Steel Sheet Metal)

Page

QVX

How to order

GN 227.6-ST-60-V7-SW

- 1 Material
- 2 Handwheel diameter d
- 3 Square S₀
- 4 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

